




















Piston rod cylinder ▶ Standard cylinders

ISO 21287, Series CCI





▶ Overview of variants

Configurable product	
	<p>The options listed in the following table are configurable. Note that not all variants can be combined with all options. Please use our Internet configurator at http://www.aventics.com or contact the nearest AVENTICS sales office.</p>

Version	Data sheet of the variant	Option: piston rod extension	Option: extended piston rod thread	Option: hollow piston rod	Option: heat resistant	Option: ATEX	Optional stroke lengths
 internal thread		✓	-	-	✓	-	✓
 external thread		✓	✓	-	✓	-	✓
 internal thread		✓	-	-	✓	-	✓
 external thread		✓	✓	-	✓	-	✓
 internal thread		✓	-	-	✓	-	✓
 external thread		✓	✓	✓	✓	-	✓
 internal thread		✓	-	-	✓	✓	✓
 external thread		✓	✓	-	✓	✓	✓
 internal thread		✓	-	-	✓	✓	✓

ISO 21287, Series CCI

▶ Overview of variants

Version	Data sheet of the variant	Option: piston rod extension	Option: extended piston rod thread	Option: hollow piston rod	Option: heat resistant	Option: ATEX	Optional stroke lengths
 external thread		✓	✓	✓	✓	✓	✓
 internal thread		-	-	-	✓	-	✓