


MAREX OS III
FOR A SAFE JOURNEY



Ship control – let your ideas run free

AVENTICS control systems can be found on all type of ships around the world. Work vessels with classification, passenger liners, coastal cargo ships and even yachts rely on engineering expertise Made in Germany.

Regardless of which propulsion concept is required – the reversing gear system, the controllable pitch propeller system, or even new drive concepts such as hybrid systems are using our most proven product: the Marex OS III.



Advantages

- ✓ Easy installation thanks to pre-assembly
- ✓ Bridge components can also be used in the outside area
- ✓ System reliability thanks to one self-monitoring CAN bus per drive train
- ✓ Approval of drawing and FAT upon request

Marex OS III – Key Features and Advantages



Design

- Unique
- Functional
- Ergonomic



Flexible

- Modular system architecture
- Independent of the type of drive
- Easy to install



Features

- No project-based programming
- Customized by parameter settings
- Optimized operating forces

Marex OS III – Benefits

Life Cycle Management


- Consultancy during design and refit
- Commissioning and training
- Service and refitting of functions with worldwide network

Consultancy by Experts


- Technical feasibility
- Project work
- Site inspection including life cycle management

Worldwide Network

- Project work
- Service
- Training
- Sales including consulting



Marex OS III – System



Integrated Functions

- Engine control, speed curves and engine stall protection
- Gear operation, reversing maneuver curves
- Control of PTO and PTI, Trolling and Slip & Grip
- Multi-engine systems
- Calculated ship speed
- Shaft brake control
- Internal software PLC to add special functions
- Standard interface for DP system, Autopilot and VDR

Marex OS III – Components

Series	Features	Pictures
Control heads	Illuminated scale, electric shaft, various designs, different propulsion plants, integrated keypad, triple-engine version available	
5.7" display	Freely configurable, 4 illuminated push buttons, digital 4-axis jog dial, readable in the sunlight, ergonomic design, 2 propulsion plants in one display	
Operating and indication modules	Indication of remote control data and data input	
Marine propulsion controllers	Single hardware component for different types of propulsion systems, preconfigured functions, software PLC function, error log with real-time stamp, integrated keypad and display	
Extension modules	VDR interface, NMEA interface, pitch controller for CPP	
Accessories	Prefabricated connecting cables and terminal blocks	
Actuators and valves	Electrical components for mechanical or pneumatic control of variables such as gear shifting, speed, or pitch setting	
Service tool	Laptop-based parameter transfer and optimization, transfer of parameters between ships within the same production line	

AVENTICS

www.marex-shipcontrols.com

marinesales@aventics.com



Germany

AVENTICS GmbH
Marine
Ulmer Straße 4
30880 Laatzen, Germany
Tel +49 511 2136-251
Fax +49 511 2136-165
www.marex-shipcontrols.com
marinesales@aventics.com

USA

AVENTICS Corporation
PO Box 13597
1953 Mercer Road (40511)
Lexington, KY 40512
Tel +1 859 254-8031
marine.us@aventics.com
www.aventics.us

China

AVENTICS Group
2002 Unit, Asdendas Plaza, No 333
Tianyaoqiao Road, Xuhui district
Shanghai, China, 200030
Tel +86 21 2426 9666
www.aventics.cn

Further contacts

www.aventics.com/contact
info@aventics.com

Your contact:



The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging.