

## Valve systems ► Base plates, according to standard

### End plate right

#### ► type C ► Reversed pressure supply permissible



00135241

Ambient temperature min./max.

Medium temperature min./max.

Medium

Working pressure min./max.

-15 °C / +50 °C

-5 °C / +50 °C

Compressed air

-0.95 bar / 16 bar

Ports separated

Materials:

Base plate

Seals

Die-cast aluminum

Acrylonitrile Butadiene Rubber

#### Technical Remarks


- The min. control pressure must be adhered to, since otherwise faulty switching and valve failure may result!
- The pressure dew point must be at least 15 °C under ambient and medium temperature and may not exceed 3 °C.
- The oil content of compressed air must remain constant during the life cycle.
- Use only the approved oils from AVENTICS, see chapter „Technical information“.

Compressed air connection				Pilot	Part No.
Input	Exhaust	Pilot control exhaust	Pilot connection		
[1]	[3 / 5]	[12]	[14]		
G 3/8	G 3/8	G 1/8	G 1/8	External	R412012469
3/8 NPTF	3/8-18 NPTF	1/8 NPTF	1/8-27 NPTF	External	R412012470
G 3/8	G 3/8	G 1/8	G 1/8	internal	<b>R412012471</b>
3/8 NPTF	3/8-18 NPTF	1/8 NPTF	1/8-27 NPTF	internal	R412012472

## End plate right

► type C ► Reversed pressure supply permissible

### Dimensions



00135255