

Preparation of compressed air ▶ Maintenance units and components

Precision pressure regulator, Series AS2-RGP-...-E11

▶ G 1/4 ▶ Qn= 2200 l/min ▶ Activation: mechanical ▶ lockable ▶ with E11 locking



00015798

Mounting orientation	Any
Working pressure min./max.	-- / 16 bar
Medium	Compressed air Neutral gases
Medium temperature min./max.	-10°C / +50°C
Ambient temperature min./max.	-10°C / +50°C
Regulator type	Diaphragm-type pressure regulator, Can be assembled into blocks
Regulator function	with relieving air exhaust
Pressure supply	single
Max. Internal air consumption	2.6 l/min
Materials:	
Housing	Polyamide
Front plate	Acrylonitrile butadiene styrene
Seals	Acrylonitrile Butadiene Rubber


Technical Remarks

- The pressure dew point must be at least 15 °C under ambient and medium temperature and may not exceed 3 °C.
- Recommended pre-filter: 5 µm
- The E11 locking is delivered without a key (see accessories for keys).
- The rear pressure gauge connection on the pressure regulator is closed with a blanking plug, the front connection is open. Depending on the customer application, a second blanking plug may be necessary. Please order separately (see accessories).

	Port	Qn	Adjustment range	Weight	Part No.
			min. - max..		
		[l/min]	[bar]	[kg]	
	G 1/4	2200	0.2 - 4	0.248	R412006146

Order pressure gauge separately
Nominal flow Qn with secondary pressure p2 = 6 bar at Δp = 1 bar

Pressure characteristics curve




p1 = Working pressure
p2 = Secondary pressure
qn = Nominal flow

Precision pressure regulator, Series AS2-RGP-...-E11


▶ G 1/4 ▶ Qn= 2200 l/min ▶ Activation: mechanical ▶ lockable ▶ with E11 locking

Flow rate characteristic (p2: 0,5 - 8 bar)



p1 = Working pressure
 p2 = Secondary pressure
 qn = Nominal flow

Dimensions



1) Order pressure gauge separately